

REF. 6551 7" SMILE MONITOR FLUSH BOX



Dimensions(width,height, depth) :198x186x44mm

In order to install the Smile monitor, it is necessary to fit a box into the wall where the monitor is to be installed. This will allow perfect integration with any setting. A decorative frame must also be added.

The flush boxes have some marks cut into the base and side which will open with a light blow or pressure, thereby allowing the passage of cables.

Available for the 7" and 3.5", Smile monitors. Select the box according to the size of the monitor.

Once fitted into the flush box, the monitor will protrude 4mm from the wall.

ACCESORIES

FEATURES

Dimensions(width,height, depth) :198x186x44mm